
AVENTICS Series CD02-AL Standardized valve systems (ISO 15407-1)

The AVENTICS Series CD02-AL complies with ISO 15407-1. The piloted controlled valves with a flow rate of up to 650 l/min consist of a robust aluminium body and are available with an individual connection plate as well as a valve system.





Technical data

Industry Industrial
Activation Electrically
Nominal flow Qn 450 I/min

Compressed air connection output VDMA 02 base plate

Min. working pressure 2 bar
Max. working pressure 10 bar
Electrical connection type Plug

Electrical connection size ISO 15217, form C

Sealing principle Soft seal
Pilot Internal
Standards ISO 15407-1

Pilot valve width 15 mm

Valve type Spool valve, positive overlapping Blocking principle Base plate principle, multiple

Connection type Plate connection

Return with spring/air spring return

Compressed air connection input VDMA 02 base plate Compressed air connection, exhaust VDMA 02 base plate Compressed air connection pilot exhaust VDMA 02 base plate

5/2-directional valve, Series CD02-AL

2023-12-13

0820038955

Basic valve equipment Basic valve without pilot valve

Frame size 18 mm

Min. control pressure 2 bar

Max. control pressure 10 bar

Min. ambient temperature 0 °C

Max. ambient temperature 50 °C

Min. medium temperature 0 °C

Max. medium temperature 60 °C

Medium Compressed air

5 µm Max. particle size Min. oil content of compressed air 0 mg/m³ Max. oil content of compressed air 5 mg/m³ Connector standard ISO 15217 Protection class with connection **IP65** 100 % Duty cycle М3 Mounting screws Weight 0.08 kg Aluminum Housing material

Seal material Acrylonitrile butadiene rubber

Hydrogenated acrylonitrile butadiene rubber

Material front plate Polyamide
Part No. 0820038955

Technical information

The min. control pressure must be adhered to, since otherwise faulty switching and valve failure may result!

The pressure dew point must be at least 15 °C less than ambient and medium temperature and may not exceed 3 °C.

The oil content of compressed air must remain constant during the life cycle.

Use only the approved oils from AVENTICS. Further information can be found in the "Technical information" document (available in https://www.emerson.com/en-us/support).

Dimensions

