
AVENTICS Series CD02-AL Standardized valve systems (ISO 15407-1)

The AVENTICS Series CD02-AL complies with ISO 15407-1. The piloted controlled valves with a flow rate of up to 650 l/min consist of a robust aluminium body and are available with an individual connection plate as well as a valve system.





Technical data

Industry Industrial
Activation Electrically
Nominal flow Qn 450 I/min

Version Closed Center

Compressed air connection output VDMA 02 base plate

Min. working pressure 2.5 bar
Max. working pressure 10 bar
Operational voltage 24 V DC
Operational voltage DC 24 V

Voltage tolerance DC -15% / +20%
Manual override without detent

Electrical connection type Plug
Electrical connection size M12
Electrical connection number of poles 3-pin
Sealing principle Soft seal
Pilot Internal
Standards ISO 15407-1

Pilot valve width 15 mm

Valve type Spool valve, positive overlapping

7472D02837

Blocking principle Base plate principle, multiple

Connection type Plate connection

Compressed air connection input VDMA 02 base plate

Compressed air connection, exhaust VDMA 02 base plate

Compressed air connection pilot exhaust VDMA 02 base plate

Power consumption DC 0.35 W Frame size 18 mm Min. control pressure 2.5 bar Max. control pressure 10 bar 0°C Min. ambient temperature 50 °C Max. ambient temperature 0°C Min. medium temperature Max. medium temperature 50 °C

Medium Compressed air

Connector standard EN 61076-2-101

Protection class with connection **IP65** TVS diode Protective circuit LED status display Yellow 100 % Duty cycle 14 ms Typ. switch-on time Typ. switch-off time 14 ms Mounting screws M3 0.12 kg Weight

Seal material Acrylonitrile butadiene rubber

Hydrogenated acrylonitrile butadiene rubber

Material front plate Polyamide
Part No. 7472D02837

Technical information

Housing material

The min. control pressure must be adhered to, since otherwise faulty switching and valve failure may result!

Aluminum

The pressure dew point must be at least 15 °C less than ambient and medium temperature and may not exceed 3 °C.

The oil content of compressed air must remain constant during the life cycle.

Use only the approved oils from AVENTICS. Further information can be found in the "Technical information" document (available in https://www.emerson.com/en-us/support).

Dimensions

