

# C40S-1004CD010

C4000 Palletizer

**SAFETY LIGHT CURTAINS** 





#### Ordering information

#### C4000 Palletizer Standard

Illustration may differ

| Resolution | Scanning<br>range | Protective field height | System part | Туре               | Part no. |
|------------|-------------------|-------------------------|-------------|--------------------|----------|
| 40 mm      | 7 m               | 1,050 mm                | Sender      | C40S-<br>1004CD010 | 1043447  |

Other models and accessories → www.sick.com/C4000\_Palletizer



#### Detailed technical data

#### **Features**

| Description             | C4000 Palletizer Standard     |
|-------------------------|-------------------------------|
| Application             | Normal industrial environment |
| System part             | Sender                        |
| Resolution              | 40 mm                         |
| Scanning range          | 7 m                           |
| Protective field height | 1,050 mm                      |
| Synchronization         | Optical synchronization       |
| Items supplied          | Sender                        |

#### Safety-related parameters

| Туре   | Type 4 (IEC 61496-1)                   |
|--|--|
| Safety integrity level   | SIL 3 (IEC 61508)                      |
| Category   | Category 4 (EN ISO 13849)              |
| Performance level  | PL e (EN ISO 13849)                    |
| $\mbox{PFH}_{\mbox{\scriptsize D}}$ (mean probability of a dangerous failure per hour) | 15 * 10 <sup>-9</sup>                  |
| T <sub>M</sub> (mission time)  | 20 years (EN ISO 13849)                |
| Safe state in the event of a fault   | At least one OSSD is in the OFF state. |

#### **Functions**

|  | Functions | Delivery status |
|--|-----------|-----------------|
| Function range                         | Standard  |                 |
| Protective operation                   | <b>√</b>  |                 |
| Beam coding                            | 1         | Code 1          |
| Configurable scanning range            | ✓         | 0.5 m 7 m       |
| Safe SICK device communication via EFI | ✓         |                 |

#### Interfaces

| System connection | Hirschmann male connector M26, 12-pin |
|-------------------|---------------------------------------|

 $<sup>^{1)}</sup>$  Depending on load, power supply and wire cross-section. The technical specifications must be observed.

| Direction of cable connection | Straight             |
|-------------------------------|----------------------|
| Conductor cross section       | 0.75 mm <sup>2</sup> |
| Permitted cable length        | 50 m <sup>1)</sup>   |
| Display elements              | 7-segment display    |

 $<sup>^{1)}</sup>$  Depending on load, power supply and wire cross-section. The technical specifications must be observed.

#### Electrical data

| Protection class              | III (IEC 61140)                       |
|-------------------------------|---------------------------------------|
| Supply voltage V <sub>S</sub> | 24 V DC (19.2 V 28.8 V) <sup>1)</sup> |
| Residual ripple               | ≤ 10 % <sup>2)</sup>                  |

<sup>1)</sup> The external voltage supply must be capable of buffering brief mains voltage failures of 20 ms as specified in EN 60204-1. Suitable power supplies are available as accessories from SICK.

#### Mechanical data

| Dimensions            | See dimensional drawing   |
|-----------------------|---------------------------|
| Housing cross-section | 48 mm x 40 mm             |
| Housing material      | Aluminum extruded profile |
| Weight                | 2,250 g                   |

#### Ambient data

| Enclosure rating              | IP65 (EN 60529)                 |
|-------------------------------|---------------------------------|
| Ambient operating temperature | 0 °C +55 °C                     |
| Storage temperature           | -25 °C +70 °C                   |
| Air humidity                  | 15 % 95 %, Non-condensing       |
| Vibration resistance          | 5 g, 10 Hz 55 Hz (EN 60068-2-6) |
| Shock resistance              | 10 g, 16 ms (EN 60068-2-27)     |

#### Other information

| Wave length   | 850 nm                         |
|---------------|--------------------------------|
| Type of light | Near-infrared (NIR), invisible |


#### Classifications

| ECLASS 5.0   | 27272704 |
|--------------|----------|
| ECLASS 5.1.4 | 27272704 |
| ECLASS 6.0   | 27272704 |
| ECLASS 6.2   | 27272704 |
| ECLASS 7.0   | 27272704 |
| ECLASS 8.0   | 27272704 |
| ECLASS 8.1   | 27272704 |
| ECLASS 9.0   | 27272704 |
| ECLASS 10.0  | 27272704 |
| ECLASS 11.0  | 27272704 |
| ECLASS 12.0  | 27272704 |
| ETIM 5.0     | EC002549 |

 $<sup>^{2)}</sup>$  Within the limits of  $V_{S}$ .

| ETIM 6.0       | EC002549 |
|----------------|----------|
| ETIM 7.0       | EC002549 |
| ETIM 8.0       | EC002549 |
| UNSPSC 16.0901 | 46171620 |

#### Dimensional drawing (Dimensions in mm (inch))



#### Illustration sender (receiver mirror image)

|       | L1    | L2    | A     |
|-------|-------|-------|-------|
| 300   | 381   | 427   | 224   |
| 450   | 532   | 578   | 374   |
| 600   | 682   | 728   | 524   |
| 750   | 833   | 879   | 674   |
| 900   | 984   | 1.030 | 824   |
| 1.050 | 1.134 | 1.180 | 974   |
| 1.200 | 1.283 | 1.329 | 1.124 |
| 1.350 | 1.435 | 1.481 | 1.274 |
| 1.500 | 1.586 | 1.632 | 1.424 |

|       | L1    | L2    | A     |
|-------|-------|-------|-------|
| 1.650 | 1.736 | 1.782 | 1.574 |
| 1.800 | 1.887 | 1.933 | 1.724 |

#### Recommended accessories

Other models and accessories → www.sick.com/C4000\_Palletizer

|              | Brief description  | Туре                         | Part no. |
|--------------|--|------------------------------|----------|
| Alignment ai | ds   |                              |          |
|              | Laser alignment aid for various sensors, laser class 2 (IEC 60825). Do not look into the beam!, 19 mm x 67.3 mm x 66.9 mm  | AR60                         | 1015741  |
|              | Adapter AR60 for housing cross-section 48 mm x 40 mm   | AR60 adapter, 48x40          | 4032461  |
|              | Adapter AR60 for housing cross-section 48 mm x 40 mm in PU3H device column   | AR60 adapter,<br>48x40, PU3H | 4056731  |
| ptics cloths |  |                              |          |
| SICK         | Cloth for cleaning optical surfaces  | Lens cloth                   | 4003353  |
| Mounting bra | ackets and plates  |                              |          |
|              | 4 pieces, Mounting kit 1, mounting bracket, rigid, L-shaped, including fixing screws and washers   | BEF-3WNGBAST4                | 7021352  |
| erminal and  | alignment brackets   |                              |          |
|              | 4 pieces, Mounting kit 6, side bracket, rotatable, zinc diecast  | BEF-1SHABAZN4                | 2019506  |
| Q            | 4 pieces, Omega bracket, rotatable, fixable with only one screw, for mounting on the swivel mount  | BEF-2SMMEAAL4                | 2044847  |
|              | 4 pieces, Mounting kit 2, rotatable, swivel mount, Polyamide PA6   | BEF-2SMMEAKU4                | 2019659  |
| Others       |  |                              |          |
|              | <ul> <li>Connection type head A: Male connector, M26, 12-pin, angled, A-coded</li> <li>Description: Unshielded</li> <li>Connection systems: Crimp contacts</li> <li>Permitted cross-section: 0.5 mm² 1.5 mm²</li> <li>Note: 12 crimping contacts enclosed</li> </ul>   | STE-<br>0612W000GA3KM0       | 6021192  |
|              | <ul> <li>Connection type head A: Male connector, M26, 12-pin, straight, A-coded</li> <li>Description: Unshielded</li> <li>Connection systems: Crimp contacts</li> <li>Permitted cross-section: 0.5 mm² 1.5 mm²</li> <li>Note: 12 crimping contacts enclosed</li> </ul> | STE-<br>0612G000GA3KM0       | 6021191  |
|              |  |                              |          |

| Brief description   | Туре                   | Part no. |
|---|------------------------|----------|
| <ul> <li>Connection type head A: Female connector, M26, 12-pin, straight, A-coded</li> <li>Description: Unshielded</li> <li>Connection systems: Crimp contacts</li> <li>Permitted cross-section: 0.5 mm² 1.5 mm²</li> <li>Note: 12 crimping contacts enclosed</li> </ul>  | DOS-<br>0612G000GA3KM0 | 6020757  |
| <ul> <li>Connection type head A: Female connector, M26, 12-pin, angled, A-coded</li> <li>Description: Unshielded</li> <li>Connection systems: Crimp contacts</li> <li>Permitted cross-section: 0.5 mm² 1.5 mm²</li> <li>Note: 12 crimping contacts enclosed</li> </ul>  | DOS-<br>0612W000GA3KM0 | 6020758  |
| <ul> <li>Connection type head A: Male connector, M8, 4-pin, straight</li> <li>Connection type head B: Male connector, USB-A, straight</li> <li>Cable: 2 m, 4-wire, PVC</li> <li>Description: Unshielded, Configuration cable with integrated RS-232 transducer on USB for connecting a sensor configuration connection (M8, 4-pin) to the USB interface of a PC</li> </ul>  | DSL-<br>8U04G02M025KM1 | 6034574  |
| <ul> <li>Connection type head A: Male connector, M8, 4-pin, straight</li> <li>Connection type head B: Male connector, USB-A, straight</li> <li>Cable: 10 m, 4-wire, PVC</li> <li>Description: Unshielded, Configuration cable with integrated RS-232 transducer on USB for connecting a sensor configuration connection (M8, 4-pin) to the USB interface of a PC</li> </ul> | DSL-<br>8U04G10M025KM1 | 6034575  |
| <ul> <li>Connection type head A: Female connector, M26, 12-pin, straight</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 20 m, 12-wire, PVC</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Connection systems: Flying leads</li> </ul>  | DOL-<br>0612G20M075KM0 | 2022549  |
| <ul> <li>Connection type head A: Female connector, M26, 12-pin, straight</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 15 m, 12-wire, PVC</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Connection systems: Flying leads</li> </ul>  | DOL-<br>0612G15M075KM0 | 2022548  |
| <ul> <li>Connection type head A: Female connector, M26, 12-pin, straight</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 10 m, 12-wire, PVC</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Connection systems: Flying leads</li> </ul>  | DOL-<br>0612G10M075KM0 | 2022547  |
| <ul> <li>Connection type head A: Female connector, M26, 12-pin, straight</li> <li>Connection type head B: Flying leads</li> <li>Cable: 5 m, PVC</li> <li>Description: Unshielded</li> <li>Connection systems: Flying leads</li> <li>Note: Without EFI: Pin 9 and 10 not connected</li> </ul>  | DOL-<br>0610G05M075KM1 | 2046888  |
| <ul> <li>Connection type head A: Female connector, M26, 12-pin, straight</li> <li>Connection type head B: Flying leads</li> <li>Cable: 10 m, PVC</li> <li>Description: Unshielded</li> <li>Connection systems: Flying leads</li> <li>Note: Without EFI: Pin 9 and 10 not connected</li> </ul>   | DOL-<br>0610G10M075KM1 | 2046889  |
| <ul> <li>Connection type head A: Female connector, M26, 12-pin, straight</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 5 m, 12-wire, PVC</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Connection systems: Flying leads</li> </ul>   | DOL-<br>0612G05M075KM0 | 2022545  |

# C40S-1004CD010 | C4000 Palletizer

SAFETY LIGHT CURTAINS

|              | Brief description   | Туре  | Part no. |
|--------------|---|-------|----------|
| Switching am | plifiers  |       |          |
|              | <ul> <li>Applications: Functionality upgrade</li> <li>Compatible sensor types: C4000 safety light curtains</li> <li>Description: Upgrades the C4000 Standard, Advanced, Palletizer, Entry/Exit, and Fusion to include the functions defined in the technical specifications, e.g., bypass, operating mode switching, and PSDI in the case of C4000 Standard, Advanced.</li> </ul> | UE402 | 1023577  |

### SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

## **WORLDWIDE PRESENCE:**

Contacts and other locations -www.sick.com

