

M40P-70A303RB0

M4000 Advanced Curtain

SAFETY LIGHT CURTAINS



Illustration may differ

Ordering information

| Resolution | Scanning range | Protective field height | System part | Туре | Part no. |
|------------|----------------|-------------------------|-------------|--------------------|----------|
| 30 mm | 21 m | 1,800 mm | Pair | M40P- 70A303RB0 | 1043304 |

Included in delivery: M40E-70A303RB0 (1), M40S-70A303AA0 (1)

Other models and accessories → www.sick.com/M4000_Advanced_Curtain



Detailed technical data

Features

| System part | Pair |
|-------------------------|-------------------------|
| Resolution | 30 mm |
| Scanning range | 21 m |
| Protective field height | 1,800 mm |
| Response time | |
| Without beam coding | 15 ms |
| With beam coding | 27 ms |
| Synchronization | Optical synchronisation |

Safety-related parameters

| Туре | Type 4 (IEC 61496-1) |
|--|--|
| Safety integrity level | SIL 3 (IEC 61508) |
| Category | Category 4 (EN ISO 13849) |
| Performance level | PL e (EN ISO 13849) |
| $\mbox{PFH}_{\mbox{\scriptsize D}}$ (mean probability of a dangerous failure per hour) | 28 * 10 ⁻⁹ (EN ISO 13849) |
| T _M (mission time) | 20 years (EN ISO 13849) |
| Safe state in the event of a fault | At least one OSSD is in the OFF state. |

Functions

| | Functions | Delivery status |
|--|-----------|---------------------|
| Restart interlock | 1 | Internal |
| External device monitoring (EDM) | 1 | Activated |
| Beam coding | 1 | Uncoded |
| Configurable status output (ADO) | 1 | Contamination (OWS) |
| Sender test | 1 | Deactivated |
| Configurable scanning range | 1 | Low scanning range |
| Safe SICK device communication via EFI | 1 | |

¹⁾ The muting functions can only be used in combination with the UE403 muting switching amplifier or a suitable safety controller (e.g., Flexi Classic, Flexi Soft).

| | Functions | Delivery status |
|---|-----------------|-----------------|
| Differentiation between man and material (muting) | ✓ ¹⁾ | |

¹⁾ The muting functions can only be used in combination with the UE403 muting switching amplifier or a suitable safety controller (e.g., Flexi Classic, Flexi Soft).

Interfaces

| System connection | |
|--------------------------|---------------------------------------|
| Connection type | Hirschmann male connector M26, 12-pin |
| Permitted cable length | \leq 50 m $^{1)}$ |
| Permitted cross-section | ≥ 0.75 mm² |
| Extension connection | Female connector M12, 5-pin |
| Configuration method | Via software |
| Configuration connection | Female connector M8, 4-pin |
| Display elements | 7-segment display, LEDs |
| Status display | LEDs |

 $^{^{1)}}$ Depending on load, power supply and wire cross-section. The technical specifications must be observed.

Electrical data

| Protection class | III (IEC 61140) |
|----------------------------|-------------------------|
| Supply voltage $V_{\rm S}$ | 24 V DC (19.2 V 28.8 V) |
| Residual ripple | ≤ 10 % ¹⁾ |

 $^{^{1)}}$ Within the limits of V_S .

Mechanical data

| Housing cross-section | 52 mm x 55.5 mm |
|-----------------------|--|
| Housing material | Aluminum alloy ALMGSI 0.5 |
| Surface treatment | Powder coated |
| Front screen material | Polycarbonate, scratch-resistant coating |

Ambient data

| Enclosure rating | IP65 (EN 60529) |
|-------------------------------|----------------------------------|
| Ambient operating temperature | -30 °C +55 °C |
| Storage temperature | -30 °C +70 °C |
| Air humidity | 15 % 95 %, Non-condensing |
| Vibration resistance | 5 g, 10 Hz 55 Hz (IEC 60068-2-6) |
| Shock resistance | 10 g, 16 ms (EN 60068-2-29) |


Other information

| wave length | 850 nm |
|-----------------|----------|
| Classifications | |
| ECLASS 5.0 | 27272704 |

| ECLA33 3.0 | 21212104 |
|--------------|----------|
| ECLASS 5.1.4 | 27272704 |
| ECLASS 6.0 | 27272704 |
| ECLASS 6.2 | 27272704 |
| ECLASS 7.0 | 27272704 |

| ECLASS 8.0 | 27272704 |
|----------------|----------|
| ECLASS 8.1 | 27272704 |
| ECLASS 9.0 | 27272704 |
| ECLASS 10.0 | 27272704 |
| ECLASS 11.0 | 27272704 |
| ECLASS 12.0 | 27272704 |
| ETIM 5.0 | EC002549 |
| ETIM 6.0 | EC002549 |
| ETIM 7.0 | EC002549 |
| ETIM 8.0 | EC002549 |
| UNSPSC 16.0901 | 46171620 |

Dimensional drawing (Dimensions in mm (inch))



| | L1 | L2 |
|-----|-----|-----|
| 300 | 387 | 416 |
| 450 | 537 | 566 |
| 600 | 687 | 716 |

| | L1 | L2 |
|-------|-------|-------|
| 750 | 837 | 866 |
| 900 | 987 | 1,016 |
| 1,050 | 1,137 | 1,166 |
| 1,200 | 1,287 | 1,316 |
| 1,350 | 1,437 | 1,466 |
| 1,500 | 1,587 | 1,616 |
| 1,650 | 1,737 | 1,766 |
| 1,800 | 1,887 | 1,916 |

Recommended accessories

Other models and accessories → www.sick.com/M4000_Advanced_Curtain

| | Brief description | Туре | Part no. | | |
|---------------------------------|---|------------------------|----------|--|--|
| Alignment aids | | | | | |
| | Laser alignment aid for various sensors, laser class 2 (IEC 60825). Do not look into the beam!, 19 mm x 67.3 mm x 66.9 mm | AR60 | 1015741 | | |
| | Adapter AR60 for M4000 and M4000 Curtain | AR60 adapter, M4000 | 4040006 | | |
| Mounting bra | Mounting brackets and plates | | | | |
| | 4 pieces, Mounting kit 1, mounting bracket, rigid, L-shaped, including fixing screws and washers | BEF-3WNGBAST4 | 7021352 | | |
| Terminal and alignment brackets | | | | | |
| | 4 pieces, Mounting kit 6, side bracket, rotatable, zinc diecast | BEF-1SHABAZN4 | 2019506 | | |
| 6 | 4 pieces, Mounting kit 12, rotatable, swivel mount | BEF-2SMGEAKU4 | 2030510 | | |
| Others | | | | | |
| | Connection type head A: Female connector, M26, 12-pin, straight, A-coded Description: Unshielded Connection systems: Crimp contacts Permitted cross-section: 0.5 mm² 1.5 mm² Note: 12 crimping contacts enclosed | DOS- 0612G000GA3KM0 | 6020757 | | |
| | Connection type head A: Male connector, M8, 4-pin, straight Connection type head B: Male connector, USB-A, straight Cable: 10 m, 4-wire, PVC Description: Unshielded, Configuration cable with integrated RS-232 transducer on USB for connecting a sensor configuration connection (M8, 4-pin) to the USB interface of a PC | DSL- 8U04G10M025KM1 | 6034575 | | |

M40P-70A303RB0 | M4000 Advanced Curtain

SAFETY LIGHT CURTAINS

| | Brief description | Туре | Part no. | | |
|-------------------|--|------------------------|----------|--|--|
| | Connection type head A: Female connector, M26, 12-pin, straight Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 20 m, 12-wire, PVC Description: Sensor/actuator cable, unshielded Connection systems: Flying leads | DOL- 0612G20M075KM0 | 2022549 | | |
| | Connection type head A: Male connector, M8, 4-pin, straight Connection type head B: Male connector, USB-A, straight Cable: 2 m, 4-wire, PVC Description: Unshielded, Configuration cable with integrated RS-232 transducer on USB for connecting a sensor configuration connection (M8, 4-pin) to the USB interface of a PC | DSL- 8U04G02M025KM1 | 6034574 | | |
| | Connection type head A: Female connector, M26, 12-pin, straight Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 15 m, 12-wire, PVC Description: Sensor/actuator cable, unshielded Connection systems: Flying leads | DOL- 0612G15M075KM0 | 2022548 | | |
| | Connection type head A: Female connector, M26, 12-pin, straight Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 10 m, 12-wire, PVC Description: Sensor/actuator cable, unshielded Connection systems: Flying leads | DOL- 0612G10M075KM0 | 2022547 | | |
| | Connection type head A: Female connector, M26, 12-pin, straight Connection type head B: Flying leads Cable: 5 m, PVC Description: Unshielded Connection systems: Flying leads Note: Without EFI: Pin 9 and 10 not connected | DOL- 0610G05M075KM1 | 2046888 | | |
| | Connection type head A: Female connector, M26, 12-pin, straight Connection type head B: Flying leads Cable: 10 m, PVC Description: Unshielded Connection systems: Flying leads Note: Without EFI: Pin 9 and 10 not connected | DOL- 0610G10M075KM1 | 2046889 | | |
| | Connection type head A: Female connector, M26, 12-pin, straight Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 5 m, 12-wire, PVC Description: Sensor/actuator cable, unshielded Connection systems: Flying leads | DOL- 0612G05M075KM0 | 2022545 | | |
| Switching am | Switching amplifiers | | | | |
| , <u>1988888.</u> | Applications: Muting switching amplifier Compatible sensor types: M4000 Advanced multiple light beam safety devices | UE403-A0930 | 1026287 | | |
| | | | | | |

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

